

CURVE data

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1.0	IMP. - C.I.	-1.0
2	NO CHG.		
3	NO CHG.		
4	NO CHG.		

20BRHC**1170**


R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.


ONE
STAGE

| |

STAGES

PUMP PERFORMANCE

EYE AREA - SQ. IN.	= 74.8	IMPELLER WT. - LBS.	= 87
WIR PER IMPELLER LB.-FT. ²	= 17.69	ONE STAGE WT. - LBS.	= 1000
MAX. SPHERE SIZE	= 1.25 IN.	ADD'L STAGE WT. - LBS.	= 475
MAX. NO. STD. STAGES	= 9	IMPELLER NUMBER	= TSL899
MAX. OPERATING - P.S.I.	= -----	DISCH. - IN.	= 14
STD. LATERAL - IN.	= .94	SUCTION - IN.	= 14
STD. SHAFT DIA. - IN.	= 2-11/16	MAX. LATERAL - IN.	= -----
MAX. SHAFT DIA. - IN.	= -----	BOWL / IMP. CONN.	= -----
MIN. SUBMERGENCE - IN.	= 36	ADD 15-7/8" PER ADDITIONAL STAGE.	



Curves reflect typical performance; refer to factory for certification.