

CURVE NO.
12-231
11-1-77


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	0	IMP.—C.I.	
2		IMP.—NI-RI	
3		BOWL—BRZ.	
4		BOWL—NI-R.	

30 DM


1180 R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 1 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 1 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES



EYE AREA — SQ. IN. = 107	IMPELLER WT.-LBS. = 198
WR ² PER IMPELLER = 68 LB.-FT. ²	ONE STAGE WT.-LBS. = 3080
MAX. SPHERE SIZE = 2 in.	ADD'L STAGE WT.-LBS. = 1605
MAX. NO. STD. STAGES = 5	IMPELLER NUMBER = 15D15
MAX. OPERATING P.S.I. = 480	DISCH. SIZES = 20
STD. LATERAL = 1.0 in.	SUCTION SIZES = BELL
STD. SHAFT DIA. = 3.188 in.	MAX. LATERAL = in.
MAX. SHAFT DIA. = 3.437 in.	BOWL CONN. FLANGED-KEYED
MIN. SUBMERGENCE = 36 in.	ADD 2'-1 1/2" " PER ADDITIONAL STAGE.



CURVE NO.

CHANGE EFFICIENCY AS FOLLOWS	NUMBER OF POINTS	FOR NUMBER OF STAGES




LAYNE & BOWLER, INC.
Memphis, Tenn.



30" DM
1180 RPM

SINGLE STAGE LABORATORY
HEAD & HORSE POWER
THRUST "K" = 49

15D15
15SK11



IMPELLER (PATTERN NO.)	<u>15D15 or 15SK11</u>
INTERMEDIATE (PATTERN NO.)	<u>15D8</u>
SHAFT SIZE (INCHES)	<u>3 3/16 - 1502 HP</u>
TUBE SIZE (INCHES)	<u>5</u>
STANDARD LATERAL (INCHES)	<u>1</u>
DISCHARGE CONNECTION (FLANGED) (INCHES)	<u>20</u>
SUCTION CONNECTION	<u>BELL</u>
IMPELLER FULL DIAMETER (INCHES)	<u>21 3/8</u>
IMPELLER EYE AREA (INCHES SQUARED)	<u>107</u>
IMPELLER EYE DIAMETER (INCHES)	<u>12 3/4</u>
IMPELLER WEIGHT (LB)	<u>225</u>
IMPELLER WR ² (LB FT. SQUARED)	<u>68</u>
MAXIMUM DIAMETER SOLID (INCHES)	<u>2</u>
MAXIMUM WORKING PRESSURE (PSI)	<u>499</u>
MAXIMUM HYDROSTATIC PRESSURE (PSI)	<u>664</u>
MAXIMUM PRESSURE (STANDARD STUDS) (PSI)	<u>317</u>
MAXIMUM STAGES (BOWL PRESSURE)	<u>5</u>
MAXIMUM STAGES (SHAFT)	<u>4</u>
BOWL WEIGHT (ONE STAGE) (LB) (NET)	<u>3060</u>
BOWL WEIGHT (ADDITIONAL STAGES) (LB) (NET)	<u>1605</u>



GPM X 1000