





No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2.0	IMP. - C.I.	-1.0
2	-1.0		
3	NO CHG.		
4	NO CHG.		

18BRHC-B**1770** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 59	IMPELLER WT. - LBS.	= 50
W.P. PER IMPELLER LB.-FT. ²	= 10.40	ONE STAGE WT. - LBS.	= 780
MAX. SPHERE SIZE	= 1.13	ADD'L STAGE WT. - LBS.	= 360
MAX. NO. STD. STAGES	= 7	IMPELLER NUMBER	= T5KB99
MAX. OPERATING - P.S.I.	= -----	DISCH. - IN.	= 12
STD. LATERAL - IN.	= 94	SUCTION - IN.	= 12
STD. SHAFT DIA. - IN.	= 2-7/16	MAX. LATERAL - IN.	= -----
MAX. SHAFT DIA. - IN.	= -----	BOWL / IMP. CONN. - IN.	= -----
MIN. SUBMERGENCE - IN.	= 26	ADD 14-1/8" PER ADDITIONAL STAGE.	



Curves reflect typical performance; refer to factory for certification.