

CURVE NO.
12-194
3-15-84


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	0	IMP.—C.I.	
2	0	IMP.—NI-RI	
3		BOWL—BRZ.	
4		BOWL—NI-R	

22GH

1180 R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES



EYE AREA — SQ. IN.	= 91.44	IMPELLER WT.-LBS.	= 95
WR ² PER IMPELLER	= 22 LB.-FT ²	ONE STAGE WT.-LBS.	= 1200
MAX. SPHERE SIZE	= 1.42 in.	ADD'L STAGE WT.-LBS.	= 550
MAX. NO. STD. STAGES	= 6	IMPELLER NUMBER	= 11G17
MAX. OPERATING P.S.I.	= 350	DISCH. SIZES	= 16"
STD. LATERAL	= 0.56 in.	SUCTION SIZES	= 22-1/2" bell
STD. SHAFT DIA.	= 2.687 in.	MAX. LATERAL	= — in.
MAX. SHAFT DIA.	= — in.	BOWL CONN.	FLANGED — KEY
MIN. SUBMERGENCE	= 30 in.	ADD 20-1/2" PER ADDITIONAL STAGE.	

