




No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1.0	IMP. - C.I.	-1.0
2	NO CHG.		
3	NO CHG.		
4	NO CHG.		

32BRMC**880**


R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES

PUMP PERFORMANCE

EYE AREA - SQ. IN.	= 169	IMPELLER WT. - LBS.	= 234
WT. PER IMPELLER LB.-FT. ²	= 178.30	ONE STAGE WT. - LBS.	= 2500
MAX. 3/4" I.D. GIZZ	= 2.13	ADOL. STAGE WT. - LBS.	= 1400
MAX. NO. STD. STAGES	= 8	IMPELLER NUMBER	= YT6P32
MAX. OPERATING - P.S.I.	=	DISCH. - IN.	= 24
STD. LATERAL - IN.	= .75	SUCTION - IN.	=
STD. SHAFT DIA. - IN.	= 4	MAX. LATERAL - IN.	=
MAX. SHAFT DIA. - IN.	=	BOWL / IMP. CONN.	=
MIN. SUBMERGENCE - IN.	= 47	ADD 23-1/2" PER ADDITIONAL STAGE	



Curves reflect typical performance; refer to factory for certification.