

CURVE data


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1.0	IMP. - C.I.	-1.0
2	NO CHG.		
3	NO CHG.		
4	NO CHG.		

36BRMC**880**


R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES

PUMP PERFORMANCE

EYE AREA - SQ. IN.	= 215	IMPELLER WT. - LBS.	= 307
WHP PER IMPELLER LB.-FT. ²	= 306.00	ONE STAGE WT. - LBS.	= 3000
MAX. SPHERE SIZE	= 2.63	ADD'L. STAGE WT. - LBS.	= 1750
MAX. NO. STD. STAGES	= 6	IMPELLER NUMBER	= YT8T92
MAX. OPERATING - P.S.I.	=	DISCH. - IN.	=
STD. LATERAL - IN.	= 0.88	SUCTION - IN.	=
STD. SHAFT DIA. - IN.	= 4.5	MAX. LATERAL - IN.	=
MAX. SHAFT DIA. - IN.	=	BOWL / IMP. CONN.	=
MIN. SUBMERGENCE - IN.	= 49	ADD 25-1/4" PER ADDITIONAL STAGE.	



Curves reflect typical performance; refer to factory for certification.