


Verli-Line


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-3	IMP - C.I.	-1
2	-1	IMP - NI-RI	-1
3	0	BOWL - BRZ	-2
4	0	BOWL - NI-R	-2

12RH**1170** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.



EYE AREA - SQ. IN.	= 25.5	IMPELLER WT. - LBS.	= 16
WPI PER IMPELLER LB.-FT. ³	= 1.3	ONE STAGE WT. - LBS.	= 410
MAX. NO. STD. STAGES	= 23	ADD'L STAGE WT. - LBS.	= 115
MAX. OPERATING - PSI	= 432	DISCH. - IN.	= 8.12
STD. LATERAL - IN.	= 0.375	SUCTION - IN.	= 8
STD. SHAFT DIA. - IN.	= 1.938	BOWL CONN. - FLANGED COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 10" PER ADDITIONAL STAGE	
MIN. SUBMERGENCE - IN.	= 20		



Curves reflect typical performance. Refer to factory for details.