


Veri-Line®

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-3	IMP. - C.I.	-1
2	-1	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-2
4	0	BOWL - NI-RI	-2


12RL**1170**

R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.



EYE AREA - SQ. IN.	= 25.5	IMPELLER WT. - LBS.	= 16
WR. PER IMPELLER LB.-FT. ²	= 1.3	ONE STAGE WT. - LBS.	= 410
MAX. NO. STD. STAGES	= 24	ADDL. STAGE WT. - LBS.	= 115
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 8.10
STD. LATERAL - IN.	= 0.375	SUCTION - IN.	= 8
STD. SHAFT DIA. - IN.	= 1.638	BOWL CONN. - FLANGED COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 1" PER ADDITIONAL STAGE	
MIN. SUBMERGENCE - IN.	= 15		



Curves reflect typical performance. refer to factory for certification