


Verli-Line®

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-4	IMP. - C.I.	-2
2	-2	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-2
6	1	BOWL - NI-R.	-2


14KHM**1170**

R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE1
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 34.6	IMPELLER WT. - LBS.	= 40
WT. PER IMPELLER LB.-FT. ²	= 3.03	ONE STAGE WT. - LBS.	= 500
MAX. SPHERE SIZE	= -----	ADDITIONAL STAGE WT. - LBS.	= 175
MAX. NO. STD. STAGES	= 20	IMPELLER NUMBER	= -----
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 10
STD. LATERAL - IN.	= 375	SUCTION - IN.	= 10
STD. SHAFT DIA. - IN.	= 1-15/16	MAX. LATERAL - IN.	= -----
MAX. SHAFT DIA. - IN.	= -----	BOWL CONN. FLANGED - COLLET	
MIN. SUBMERGENCE - IN.	= 26	ADD 11" PER ADDITIONAL STAGE.	



VL1170-14KHM1110