

CURVE data

Verli-Line®


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1.5	IMP. - C.I.	-1
2	0	IMP. - NI-RI	-1
3		BOWL - BRZ.	-2
4		BOWL - NI-R.	-2

16AWM**1200**


R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES

PUMP PERFORMANCE

EYE AREA - SQ. IN.	= 51.2	IMPELLER WT. - LBS.	= 45
WT. PER IMPELLER LB.-FT. ²	= 7.2	ONE STAGE WT. - LBS.	= 400
MAX. SPHERE SIZE	= -----	ADDL. STAGE WT. - LBS.	= 250
MAX. NO. STD. STAGES	= 4	IMPELLER NUMBER	= -----
MAX. OPERATING - P.S.I.	= 300	DISCH. - IN.	= 12, 14
STD. LATERAL - IN.	= 44	SUCTION - IN.	= 17-1/4" BELL
STD. SHAFT DIA. - IN.	= 2.187	MAX. LATERAL - IN.	= -----
MAX. SHAFT DIA. - IN.	= -----	BOWL CONN. - FLANGED - COLLET	
MIN. SUBMERGENCE - IN.	= 32	ADD 15-1/4" PER ADDITIONAL STAGE	



Curves reflect typical performance; refer to factory for certification

VL 20016AWM1110