

Verli-Line


No Stages	Eff Change	MATERIAL	Eff Change
1	-4	IMP. - C.I.	-1
2	-2	IMP. - NI-RI	-1
3	-1	BOWL - BRZ.	-2
4	0	BOWL - NI-R.	-2

16KHM**1170** R.P.M.


SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 4 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 4 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE()
STAGES**PUMP PERFORMANCE****K = 20.6**

IMP. DIA.
A = 12.188
B = 11.250
C = REFER TO
FACTORY



EYE AREA - SQ. IN.	= 48.3	IMPELLER WT. - LBS.	= 34
WR. PER IMPELLER LB. FT. ²	= 4.65	ONE STAGE WT. - LBS.	= 600
MAX. NO. STD. STAGES	= 15	ADDL. STAGE WT. - LBS.	= 225
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 12
STD. LATERAL - IN.	= 0.440	SUCTION - IN.	= BELL
STD. SHAFT DIA. - IN.	= 2.188	BOWL CONN. FLANGED-COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 12" PER ADDITIONAL STAGE.	
MIN. SUBMERGENCE - IN.	= 32		



Curves reflect typical performance; refer to factory for certification.