


Verli-Line


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1	IMP. - C.I.	-2
2	0	IMP. - NI-RI	-2
3		BOWL - BRZ	-1
4		BOWL - NI-RI	-11/2

18 AWM**1180** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE1
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 59	IMPELLER WT. - LBS.	= 75
WRP PER IMPELLER LB.-F.T.	= 10.2	ONE STAGE WT. - LBS.	= 500
MAX. SPHERE SIZE	= ---	ADD'L STAGE WT. - LBS.	= 350
MAX. NO. STD. STAGES	= 6	IMPELLER NUMBER	= ---
MAX. OPERATING - P.S.I.	= 300	DISCH. - IN.	= 14, 12
STD. LATERAL - IN.	= 0.38	SUCTION - IN.	= 17 1/4 BELL
STD. SHAFT DIA. - IN.	= 2.187	MAX. LATERAL - IN.	= ---
MAX. SHAFT DIA. - IN.	= ---	BOWL CONN. FLANGED - COLLET	
MIN. SUBMERGENCE - IN.	= 30	ADD 16 1/2" PER ADDITIONAL STAGE	



Curves reflect typical performance. refer to factory for certification