


CURVE data

Verli-Line®


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1	IMP. - C.I.	-1
2	0	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-1
4	0	BOWL - NI-R.	-1

28SKKL**1170** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 135.5	IMPELLER WT. - LBS.	= 190
WHP PER IMPELLER LB.-FT. ²	= 51.5	ONE STAGE WT. - LBS.	= 2300
MAX NO. STD. STAGES	= 3	ADD'L STAGE WT. - LBS.	= 920
MAX. OPERATING - P.S.I.	= 200	DISCH. - IN.	= 16, 20
STD. SHAFT DIA. - IN.	= 2.688	SUCTION - IN.	= BELL
MAX. SHAFT DIA. - IN.	= --	BOWL CONN. FLANGED-COLLET	
MIN. SUBMERGENCE - IN.	= 56	ADD 22.75" PER ADDITIONAL STAGE.	



Curves reflect typical performance; refer to factory for certification