


CURVE data**Veri-Line®**

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1	IMP. - C.I.	-1
2	0	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-1
4	0	BOWL - NI-R.	-1


28SKKS**1170**

R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.



EYE AREA - SQ. IN.	= CONSULT FACT.	IMPELLER WT. - LBS.	= 190
WPI PER IMPELLER LB.-FT. ²	= 67.8	ONE STAGE WT. - LBS.	= 2300
MAX. NO. STD. STAGES	= 1	ADDL. STAGE WT. - LBS.	= 820
MAX. OPERATING - P.S.I.	= 200	DISCH. - IN.	= 16, 20
STD. SHAFT DIA. - IN.	= 2.688	SUCTION - IN.	= BELL
MAX. SHAFT DIA. - IN.	= —	BOWL CONN.	FLANGED COLLET
MIN. SUBMERGENCE - IN.	= 60	ADD 22.75" PER ADDITIONAL STAGE	



Curves reflect typical performance, refer to factory for certification.