


CURVE data

Verli-Line®

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2	IMP. - C.I.	-1
2	0	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-1
4	0	BOWL - NI-R.	-1


30KL**1170** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.



EYE AREA - SQ. IN.	= 173.75
W.P. PER IMPELLER LB. FT. ²	= 122.0
MAX. NO. STD. STAGES	= 3
MAX. OPERATING - P.S.I.	= 300
STD. SHAFT DIA. - IN.	= 3.25
MAX. SHAFT DIA. - IN.	= —
MIN. SUBMERGENCE - IN.	= 60

IMPELLER WT. - LBS.	= 246
ONE STAGE WT. - LBS.	= 3000
ADD'L STAGE WT. - LBS.	= 1500
DISCH. - IN.	= 16, 20
SUCTION - IN.	= BELL
BOWL CONN.	FLANGED-KEYED
ADD 28.5' PER ADDITIONAL STAGE	



Curves reflect typical performance. refer to factory for certification