


Verli-Line®


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2	IMP. - C.I.	-1
2	-1	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-2
4		BOWL - NI-RI	-1

13 MKM**1770** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE STAGE ()
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 25.5	IMPELLER WT. - LBS.	= 17.5
WPI PER IMPELLER LB.-FT. ²	= 1.45	ONE STAGE WT. - LBS.	= 278
MAX. NO. STD. STAGES	= 8	ADD'L STAGE WT. - LBS.	= 116
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 6.10
STD. LATERAL - IN.	= 0.64	SUCTION - IN.	= 10
STD. SHAFT DIA. - IN.	= 1.687	BOWL CONN. FLANGED - COLLET	
MIN. SUBMERGENCE - IN.	= 41	ADD 11.38" PER ADDITIONAL STAGE.	



Curves reflect typical performance, refer to factory for certification