

CURVE data

Verli-Line®

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-3	IMP. - C.I.	-1
2	-1.5	IMP. - NI-RI	-1
3	-1	BOWL - BRZ.	-2
4	0	BOWL - NI-R.	-2


14FHM

1770 R.P.M.


SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 4 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 4 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE ()
STAGE STAGES

PUMP PERFORMANCE



EYE AREA - SQ. IN.	= 56	IMPELLER WT. - LBS.	= 26
WR/PER IMPELLER LB.-FT. ²	= 2.9	ONE STAGE WT. - LBS.	= 650
MAX. NO. STD. STAGES	= 3	ADDL STAGE WT. - LBS.	= 240
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 12
STD. LATERAL - IN.	= 0.560	SUCTION - IN.	= 12
STD. SHAFT DIA. - IN.	= 2.188	BOWL CONN. - FLANGED COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 12.313" PER ADDITIONAL STAGE.	
MIN. SUBMERGENCE - IN.	= 36		



Curves reflect typical performance. refer to factory for verification