

Verli-Line®


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-4	IMP. - C.I.	-1
2	-2	IMP. - NI-RI	-1
3	-1	BOWL - BRZ.	-2
4	0	BOWL - NI-RI	-2

14RM**1770** R.P.M.


SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 4 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 4 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE**PUMP PERFORMANCE****K = 15.5**

IMP. DIA.
A = 11.500
B = 11.000
C = 10.500



EYE AREA - SQ. IN.	= 41.2	IMPELLER WT. - LBS.	= 26
WR' PER IMPELLER LB.-FT.'	= 4.15	ONE STAGE WT. - LBS.	= 700
MAX. NO. STD. STAGES	= 6	ADD'L STAGE WT. - LBS.	= 265
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 12
STD. LATERAL - IN.	= 9.739	SUCTION - IN.	= 10
STD. SHAFT DIA. - IN.	= 2.188	BOWL CONN. FLANGED-COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 13.375" PER ADDITIONAL STAGE	
MIN. SUBMERGENCE - IN.	= 30		



Curves reflect typical performance, refer to factory for certification.