


CURVE data**Veri-Line®**


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-3	IMP. - C.I.	-1
2	-2	IMP. - NI-RI	-1
3	-1	BOWL - BRZ.	-3
4	0	BOWL - NI-R.	-3

6 AWH**1750** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 4 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 4 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE ()
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 6.28	IMPELLER WT. - LBS.	= 2.3
WR. PER IMPELLER LB.-FT. ²	= 0.03	ONE STAGE WT. - LBS.	= 60
MAX. NO. STD. STAGES	= 15	ADD'L. STAGE WT. - LBS.	= 16
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 4
STD. LATERAL - IN.	= 0.25	SUCTION - IN.	= 4
STD. SHAFT DIA. - IN.	= 1.00	BOWL CONN. THREADED - COLLET	
MIN. SUBMERGENCE - IN.	= 10	ADD 5-1/4" PER ADDITIONAL STAGE.	



Curves reflect typical performance; refer to factory for certification.