


CURVE data**Verli-Line™**


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2	IMP - C.I.	-1
2	-1	IMP - NI-RI	-1
3	0	BOWL - BRZ	-2
4	0	BOWL - NI-R	-2

8RL**1750**
R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE
STAGE ()
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 10.4	IMPELLER WT. - LBS.	= 10
WV PER IMPELLER LB.-FT. ³	= 0.160	ONE STAGE WT. - LBS.	= 140
MAX NO. STD. STAGES	= 28	ADDL. STAGE WT. - LBS.	= 45
MAX. OPERATING - P.S.I.	= 400	DISCH. - IN.	= 6
STD. LATERAL - IN.	= 0.375	SUCTION - IN.	= 5
STD. SHAFT DIA. - IN.	= 1.188	BOWL CONN. - FLANGED-COLLET	
MAX. SHAFT DIA. - IN.	= —	ADD 6.5" PER ADDITIONAL STAGE	
MIN. SUBMERGENCE - IN.	= 11		



* ADD 3 1/2 IN. FOR THREADED SUCTION CASE

Curves reflect typical performance, refer to factory for certification.