


CURVE data**Veri-Line®**


No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2	IMP. - C.I.	-2
2	-2	IMP. - NI-RI	-1
3	-1	BOWL - BRZ.	0
4	0	BOWL - NI-R.	-1

6 BHHC**3500 R.P.M.**

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 4 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 4 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE STAGE ()
STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 4.32	IMPELLER WT. - LBS.	= 2.4
WR² PER IMPELLER LB.-FT.²	= 0.03	ONE STAGE WT. - LBS.	= 100
MAX. NO. STD. STAGES	= 17	ADD'l STAGE WT. - LBS.	= 25
MAX. OPERATING - P.S.I.	= 530	DISCH. - IN.	= 4
STD. LATERAL - IN.	= 0.50	SUCTION - IN.	= 4
STD. SHAFT DIA. - IN.	= 1.00	BOWL CONN. THREADED - COLLET	
MIN. SUBMERGENCE - IN.	= 27	ADD 4-1/4" PER ADDITIONAL STAGE	



Curves reflect typical performance. refer to factory for certification