

CURVE data**Verli-Line®**

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-2	IMP. - C.I.	-1
2	-1	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-1
4	0	BOWL - NI-R	-1


36EHL**710** R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 3 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 3 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.


ONE STAGE () STAGES

PUMP PERFORMANCE**K = 93.0**

IMP. DIA.
A = REFER TO FACTORY
B = REFER TO FACTORY
C = REFER TO FACTORY



EYE AREA - SQ. IN.	= 210.0	IMPELLER WT. - LBS.	= 440
W.P. PER IMPELLER LB.-FT. ²	= 240.0	ONE STAGE WT. - LBS.	= 4500
MAX. NO. STD. STAGES	= 3	ADD'L STAGE WT. - LBS.	= 2000
MAX. OPERATING - P.S.I.	= 200	DISCH. - IN.	= 20.24
STD. SHAFT DIA. - IN.	= 3.25	SUCTION - IN.	= BELL
MAX. SHAFT DIA. - IN.	= —	BOWL CONN. FLANGED-KEYED	
MIN. SURGERGENCE - IN.	= 60	ADD 29.313" PER ADDITIONAL STAGE.	



* ADD. 0 IN. FOR THREADED SUCTION CASE

Curves reflect typical performance; refer to factory for certification.