

CURVE data


Verli-Line®

No. Stages	Eff. Change	MATERIAL	Eff. Change
1	-1	IMP. - C.I.	-1
2	0	IMP. - NI-RI	-1
3	0	BOWL - BRZ.	-1
4	0	BOWL - NI-R.	-1


28SKKL**880**

R.P.M.

SINGLE STAGE LAB PERFORMANCE WITH STANDARD MATERIALS. EFFICIENCY SHOWN FOR 2 OR MORE STAGES. HORSE POWER SHOWN FOR ONE STAGE BASED ON 2 STAGE EFFICIENCY. CORRECTIONS SHOULD BE MADE FOR STAGES AND MATERIAL.

ONE (1)
STAGE STAGES**PUMP PERFORMANCE**

EYE AREA - SQ. IN.	= 135.5	IMPELLER WT. - LBS.	= 190
WRP PER IMPELLER LB.-FT. ³	= 61.6	ONE STAGE WT. - LBS.	= 2300
MAX. NO. STD. STAGES	= 5	ADD'L. STAGE WT. - LBS.	= 920
MAX. OPERATING - P.S.I.	= 200	DISCH. - IN.	= 16.20
STD. SHAFT DIA. - IN.	= 2.688	SUCTION - IN.	= BELL
MAX. SHAFT DIA. - IN.	= —	BOWL CONN. FLANGED-COLLET	
MIN. SUBMERGENCE - IN.	= 48	ADD 22.75" PER ADDITIONAL STAGE.	



Curves reflect typical performance, refer to factory for confirmation